

Special Track Work Mold Only, Power, 250 kcmil Ropelay, Left Hand

Data Solutions

KATALOGNUMMER

PBJT52WLHM



FUNKTIONER

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

PRODUKTEGENSKABER

Materiale: Graphite

Bond Terminal Style: J

Rail Type: Crane Rail Profiles

Conductor Size: 250 kcmil Ropelay

Conductor Outer Diameter, Nominal: 19.05mm

Welder Style: T5

Orientation: Left Hand

Mold Only: Yes

Welding Material: PB90 or PB90PLUSF80, Sold Separately

Handle Clamp: B323BX, Sold Separately

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE