

# Intelligent PDU, EN6xxx, 230 VAC, 1-PH

## Data Solutions

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



### FUNKTIONER

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

### SPECIFIKATIONER

Table 1/6

| Katalognummer | Produktfamilie | Type            | Product Type | Stiktype                           | Socket Quantity | Farve |
|---------------|----------------|-----------------|--------------|------------------------------------|-----------------|-------|
| EN6326        | Enlogic        | Intelligent PDU | Socket Strip | (20) C13, (4) C19                  | 24              | Black |
| EN6325        | Enlogic        | Intelligent PDU | Socket Strip | (20) C13, (4) C19                  | 24              | Black |
| EN6329        | Enlogic        | Intelligent PDU | Socket Strip | (24) C13, (8) C19                  | 32              | Black |
| EN6350        | Enlogic        | Intelligent PDU | Socket Strip | (20) C13/C15, (20) C13/C15/C19/C21 | 40              | Black |

| Katalognummer | Produktfamilie | Type            | Product Type | Stiktype                                           | SocketQuantity | Farve |
|---------------|----------------|-----------------|--------------|----------------------------------------------------|----------------|-------|
| EN6380        | Enlogic        | Intelligent PDU | Socket Strip | (16) Locking C13/C15, (16) Locking C13/C15/C19/C21 | 32             | Black |
| EN6337        | Enlogic        | Intelligent PDU | Socket Strip | (38) C13, (6) C19                                  | 44             | Black |

| Table 2/6     |                      |                  |                          |              |                      |               |
|---------------|----------------------|------------------|--------------------------|--------------|----------------------|---------------|
| Katalognummer | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating | Input Cable Location | Input Voltage |
| EN6326        | 16 A, 1-pole, Hy-Mag | Yes              | 0                        |              | Top Feed             | 200 – 240V    |
| EN6325        | 16 A, 1-pole, Hy-Mag | Yes              | 2                        | 7.4 kVA      | Top Feed             | 200 – 240V    |
| EN6329        | 16 A, 1-pole, Hy-Mag | Yes              | 2                        | 7.4 kVA      | Top Feed             | 200 – 240V    |
| EN6350        | 20 A, 1-pole, Hy-Mag | Yes              | 2                        | 7.4 kVA      | Top Feed             | 200 – 240V    |
| EN6380        | 20 A, 1-pole, Hy-Mag | Yes              | 2                        | 7.4 kVA      | Top Feed             | 200 – 240V    |
| EN6337        | 16 A, 1-pole, Hy-Mag | Yes              | 2                        |              | Top Feed             | 200 – 240V    |

| Table 3/6     |       |                  |                 |                  |                        |                |
|---------------|-------|------------------|-----------------|------------------|------------------------|----------------|
| Katalognummer | Phase | Interrupt Rating | Max Power Input | Nominel spænding | On/Off Switch Included | Output Voltage |
| EN6326        | 1 PH  | 5kAIC            | 3.68 kVA        |                  |                        | 200 – 240VAC   |
| EN6325        | 1 PH  | 5kAIC            | 7.44 kVA        | 230V             | Yes                    | 230VAC         |
| EN6329        | 1 PH  | 5kAIC            | 7.44 kVA        | 230V             | Yes                    | 230VAC         |
| EN6350        | 1 PH  | 5kAIC            | 7.44 kVA        | 230V             | Yes                    | 230VAC         |
| EN6380        | 1 PH  | 5kAIC            | 7.44 kVA        | 230V             | Yes                    | 230VAC         |
| EN6337        | 1 PH  | 5kAIC            | 7.44 kVA        |                  |                        | 200 – 240VAC   |

Table 4/6

| Katalognummer | Amperage<br>(Derated<br>Amperage) | Plug Type                 | Rack Units | Removable<br>Input Cable | Metering Type | Materiale |
|---------------|-----------------------------------|---------------------------|------------|--------------------------|---------------|-----------|
| EN6326        | 16 A                              | IEC 60309<br>316P6 (IP44) | 0U         | No                       | Outlet        |           |
| EN6325        | 32 A                              | IEC 60309<br>332P6 (IP44) | 0U         | No                       | Outlet        | Stål      |
| EN6329        | 32 A                              | IEC 60309<br>332P6 (IP44) | 0U         | No                       | Outlet        | Stål      |
| EN6350        | 32 A                              | IEC 60309<br>332P6 (IP44) | 0U         | No                       | Outlet        | Stål      |
| EN6380        | 32 A                              | IEC 60309<br>332P6 (IP44) | 0U         | No                       | Outlet        | Stål      |
| EN6337        | 32 A                              | IEC 60309<br>332P6 (IP44) | 0U         | No                       | Outlet        |           |

Table 5/6

| Katalognummer | Finish                   | Højde  | Bredde | Dybde | Vægt   | Pakke mængde |
|---------------|--------------------------|--------|--------|-------|--------|--------------|
| EN6326        |                          |        |        |       |        | 1            |
| EN6325        | Struktur<br>Pulvermaling | 1780mm | 52mm   | 53mm  | 9kg    | 1            |
| EN6329        | Struktur<br>Pulvermaling | 1780mm | 52mm   | 53mm  | 9.44kg | 1            |
| EN6350        | Struktur<br>Pulvermaling | 1490mm | 56mm   | 75mm  | 9.22kg | 1            |
| EN6380        | Struktur<br>Pulvermaling | 1490mm | 56mm   | 75mm  |        | 1            |
| EN6337        |                          |        |        |       |        | 1            |

Table 6/6

| Katalognummer | Input Cable Length |
|---------------|--------------------|
| EN6326        |                    |
| EN6325        | 3m                 |

| Katalognummer | Input Cable Length |
|---------------|--------------------|
| EN6329        | 3m                 |
| EN6350        | 3m                 |
| EN6380        | 3m                 |
| EN6337        |                    |

## YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**