

Varistar Colocation Cabinet, RAL 7035

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 7035 to accommodate servers while separating access and cabling of the compartments.

CERTIFICERINGER



FUNKTIONER

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 7035

SPECIFIKATIONER

Product Type: Rack

Frame Material: Stål

Table 1/3

Katalognummer	Rack Height	Højde	Cladding Material	Frame Color	Bredde	Frame Color Code
---------------	-------------	-------	-------------------	-------------	--------	------------------

11130-202	40U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-203	39U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-204	40U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-205	40U	2000mm	Stål	Light Grey	800mm	RAL 7021
11130-206	39U	2000mm	Stål	Light Grey	800mm	RAL 7035
11130-207	40U	2000mm	Stål	Light Grey	800mm	RAL 7021
11130-208	44U	2200mm	Stål	Light Grey	600mm	RAL 7021
11130-209	45U	2200mm	Stål	Light Grey	600mm	RAL 7021
11130-210	44U	2200mm	Stål	Light Grey	600mm	RAL 7021
11130-211	44U	2200mm	Stål	Light Grey	800mm	RAL 7021
11130-212	45U	2200mm	Stål	Black Grey	800mm	RAL 7021
11130-213	44U	2200mm	Stål	Light Grey	800mm	RAL 7021
11130-214	40U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-215	39U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-216	40U	2000mm	Stål	Light Grey	600mm	RAL 7021
11130-217	40U	2000mm	Stål	Light Grey	800mm	RAL 7021
11130-218	39U	2000mm	Stål	Black Grey	800mm	RAL 7021
11130-219	40U	2000mm	Stål	Light Grey	800mm	RAL 7021
11130-220	44U	2200mm	Stål	Light Grey	600mm	RAL 7021

11130-221	45U	2200mm	Stål	Light Grey	600mm	RAL 7021
11130-222	44U	2200mm	Stål	Light Grey	600mm	RAL 7021
11130-223	44U	2200mm	Stål	Light Grey	800mm	RAL 7021
11130-224	45U	2200mm	Stål	Light Grey	800mm	RAL 7021
11130-225	44U	2200mm	Stål	Light Grey	800mm	RAL 7021
11130-257	45U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-258	48U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-259	48U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-260	45U	2450mm	Stål	Light Grey	800mm	RAL 7021
11130-261	48U	2450mm	Stål	Light Grey	800mm	RAL 7021
11130-262	48U	2450mm	Stål	Light Grey	800mm	RAL 7021
11130-269	45U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-270	48U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-271	48U	2450mm	Stål	Light Grey	600mm	RAL 7021
11130-272	45U	2450mm	Stål	Light Grey	800mm	RAL 7021
11130-273	48U	2450mm	Stål	Light Grey	800mm	RAL 7021
11130-274	48U	2450mm	Stål	Light Grey	800mm	RAL 7021

Table 2/3

Katalognummer	Cladding Color	Cladding Color Code	Dybde	Pakke mængde	Number of Compartments	Finish
---------------	----------------	---------------------	-------	--------------	------------------------	--------

11130-202	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-203	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-204	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-205	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-206	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-207	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-208	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-209	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-210	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-211	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-212	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-213	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-214	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling
11130-215	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-216	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling
11130-217	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling
11130-218	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-219	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling
11130-220	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling

11130-221	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-222	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling
11130-223	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling
11130-224	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-225	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling
11130-257	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-258	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-259	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-260	Light Grey	RAL 7035	1000mm	1	2	Struktur Pulvermaling
11130-261	Light Grey	RAL 7035	1000mm	1	3	Struktur Pulvermaling
11130-262	Light Grey	RAL 7035	1000mm	1	4	Struktur Pulvermaling
11130-269	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling
11130-270	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-271	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling
11130-272	Light Grey	RAL 7035	1200mm	1	2	Struktur Pulvermaling
11130-273	Light Grey	RAL 7035	1200mm	1	3	Struktur Pulvermaling
11130-274	Light Grey	RAL 7035	1200mm	1	4	Struktur Pulvermaling

Table 3/3

Katalognummer	Materiale	Static Load
11130-202	Stål	800kg

Katalognummer	Materiale	Static Load
11130-203	Stål	800kg
11130-204	Stål	800kg
11130-205	Stål	800kg
11130-206	Stål	800kg
11130-207	Stål	800kg
11130-208	Stål	800kg
11130-209	Stål	800kg
11130-210	Stål	800kg
11130-211	Stål	800kg
11130-212	Stål	800kg
11130-213	Stål	800kg
11130-214	Stål	800kg
11130-215	Stål	800kg
11130-216	Stål	800kg
11130-217	Stål	800kg
11130-218	Stål	800kg
11130-219	Stål	800kg
11130-220	Stål	800kg

Katalognummer	Materiale	Static Load
11130-221	Stål	800kg
11130-222	Stål	800kg
11130-223	Stål	800kg
11130-224	Stål	800kg
11130-225	Stål	800kg
11130-257	Stål	800kg
11130-258	Stål	800kg
11130-259	Stål	800kg
11130-260	Stål	800kg
11130-261	Stål	800kg
11130-262	Stål	800kg
11130-269	Stål	800kg
11130-270	Stål	800kg
11130-271	Stål	800kg
11130-272	Stål	800kg
11130-273	Stål	800kg
11130-274	Stål	800kg

YDERLIGERE PRODUKTOPLYSNINGER

Side panel must be ordered separately. For suitable cable panel see Accessories.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE