

Varistar Colocation Cabinet, RAL 9003

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 9003 to accommodate servers while separating access and cabling of the compartments.

CERTIFICERINGER



FUNKTIONER

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 9003

SPECIFIKATIONER

Product Type: Rack

Frame Material: Stål

Table 1/3

Katalognummer	Rack Height	Højde	Cladding Material	Frame Color	Bredde	Frame Color Code
---------------	-------------	-------	-------------------	-------------	--------	------------------

12130-202	40U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-203	39U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-204	40U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-205	40U	2000mm	Stål	Signal White	800mm	RAL 7021
12130-206	39U	2000mm	Stål	Black Grey	800mm	RAL 7021
12130-207	40U	2000mm	Stål	Signal White	800mm	RAL 7021
12130-208	44U	2200mm	Stål	Signal White	600mm	RAL 7021
12130-209	45U	2200mm	Stål	Signal White	600mm	RAL 7021
12130-210	44U	2200mm	Stål	Signal White	600mm	RAL 7021
12130-211	44U	2200mm	Stål	Signal White	800mm	RAL 7021
12130-212	45U	2200mm	Stål	Black Grey	800mm	RAL 7021
12130-213	44U	2200mm	Stål	Signal White	800mm	RAL 7021
12130-214	40U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-215	39U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-216	40U	2000mm	Stål	Signal White	600mm	RAL 7021
12130-217	40U	2000mm	Stål	Signal White	800mm	RAL 7021
12130-218	39U	2000mm	Stål	Black Grey	800mm	RAL 7021
12130-219	40U	2000mm	Stål	Signal White	800mm	RAL 7021
12130-220	44U	2200mm	Stål	Signal White	600mm	RAL 7021

12130-221	45U	2200mm	Stål	Signal White	600mm	RAL 7021
12130-222	44U	2200mm	Stål	Signal White	600mm	RAL 7021
12130-223	44U	2200mm	Stål	Signal White	800mm	RAL 7021
12130-224	45U	2200mm	Stål	Signal White	800mm	RAL 7021
12130-225	44U	2200mm	Stål	Signal White	800mm	RAL 7021
12130-257	45U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-258	48U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-259	48U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-260	45U	2450mm	Stål	Signal White	800mm	RAL 7021
12130-261	48U	2450mm	Stål	Signal White	800mm	RAL 7021
12130-262	48U	2450mm	Stål	Signal White	800mm	RAL 7021
12130-269	45U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-270	48U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-271	48U	2450mm	Stål	Signal White	600mm	RAL 7021
12130-272	45U	2450mm	Stål	Signal White	800mm	RAL 7021
12130-273	48U	2450mm	Stål	Signal White	800mm	RAL 7021
12130-274	48U	2450mm	Stål	Signal White	800mm	RAL 7021

Table 2/3

Katalognummer	Cladding Color	Cladding Color Code	Dybde	Pakke mængde	Number of Compartments	Finish
---------------	----------------	---------------------	-------	--------------	------------------------	--------

12130-202	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-203	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-204	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-205	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-206	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-207	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-208	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-209	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-210	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-211	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-212	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-213	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-214	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling
12130-215	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-216	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling
12130-217	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling
12130-218	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-219	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling
12130-220	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling

12130-221	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-222	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling
12130-223	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling
12130-224	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-225	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling
12130-257	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-258	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-259	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-260	Signal White	RAL 9003	1000mm	1	2	Struktur Pulvermaling
12130-261	Signal White	RAL 9003	1000mm	1	3	Struktur Pulvermaling
12130-262	Signal White	RAL 9003	1000mm	1	4	Struktur Pulvermaling
12130-269	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling
12130-270	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-271	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling
12130-272	Signal White	RAL 9003	1200mm	1	2	Struktur Pulvermaling
12130-273	Signal White	RAL 9003	1200mm	1	3	Struktur Pulvermaling
12130-274	Signal White	RAL 9003	1200mm	1	4	Struktur Pulvermaling

Table 3/3

Katalognummer	Materiale	Static Load
12130-202	Stål	800kg

Katalognummer	Materiale	Static Load
12130-203	Stål	800kg
12130-204	Stål	800kg
12130-205	Stål	800kg
12130-206	Stål	800kg
12130-207	Stål	800kg
12130-208	Stål	800kg
12130-209	Stål	800kg
12130-210	Stål	800kg
12130-211	Stål	800kg
12130-212	Stål	800kg
12130-213	Stål	800kg
12130-214	Stål	800kg
12130-215	Stål	800kg
12130-216	Stål	800kg
12130-217	Stål	800kg
12130-218	Stål	800kg
12130-219	Stål	800kg
12130-220	Stål	800kg

Katalognummer	Materiale	Static Load
12130-221	Stål	800kg
12130-222	Stål	800kg
12130-223	Stål	800kg
12130-224	Stål	800kg
12130-225	Stål	800kg
12130-257	Stål	800kg
12130-258	Stål	800kg
12130-259	Stål	800kg
12130-260	Stål	800kg
12130-261	Stål	800kg
12130-262	Stål	800kg
12130-269	Stål	800kg
12130-270	Stål	800kg
12130-271	Stål	800kg
12130-272	Stål	800kg
12130-273	Stål	800kg
12130-274	Stål	800kg

YDERLIGERE PRODUKTOPLYSNINGER

Side panel must be ordered separately. For suitable cable panel see Accessories.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE