

Varistar CP Server Cabinet With Castors

Data Solutions



Welded steel frame for high dynamic load requirements.
Prepared for 19" integration of IT assets.

FUNKTIONER

Preconfigured, ready to use cabinet

High dynamic load 1000 kg with integrated castors, static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFIKATIONER

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Stål

Table 1/2

Katalognummer	Rack Height	Højde	Cladding Material	Bredde	Cladding Color	Dybde
---------------	-------------	-------	-------------------	--------	----------------	-------

10630-021	42U	2000mm	Stål	600mm	Black Grey	1200mm
10630-022	42U	2000mm	Stål	800mm	Black Grey	1200mm

Table 2/2

Katalognummer	Pakke mængde	Dynamic Load	Finish	Materiale	Type
10630-021	1	1000kgf	Struktur Pulvermaling	Stål	Mobile
10630-022	1	1000kgf	Struktur Pulvermaling	Stål	Mobile

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE