

Varistar CP Steel Door, Plain With 1-Point Locking

Data Solutions



Varistar CP Steel Door, IP 20 with Single Point Locking.

FUNKTIONER

Steel door with single point locking for IP 20 protection class

Opening angle 180°

SPECIFIKATIONER

Product Type: Cabinet Door

Beskyttelsesgrad: IP20

Materiale: Stål

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Locking Type	Pakke mængde	Farve
21630-002	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-003	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-004	52U	2450mm	600mm	Single Point Locking	1	Black Grey
21630-009	42U	2000mm	800mm	Single Point Locking	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Locking Type	Pakke mængde	Farve
21630-010	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-011	52U	2450mm	800mm	Single Point Locking	1	Black Grey
21630-400	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-401	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-402	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-403	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-404	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-405	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-406	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-407	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-493	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-494	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-495	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-496	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-497	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-498	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-499	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-500	38U	1800mm	800mm	Single Point Locking	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Locking Type	Pakke mængde	Farve
21630-501	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-502	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-503	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-504	47U	2200mm	800mm	Single Point Locking	1	Black Grey

Table 2/2

Katalognummer	Farvekode	Complies With	Finish	Type	Works With
21630-002	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-003	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-004	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-009	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-010	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-011	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-400	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-401	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-402	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-403	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-404	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-405	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-406	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP

Katalognummer	Farvekode	Complies With	Finish	Type	Works With
21630-407	RAL 7021	IEC 61587-1, IEC 61587-3	Struktur Pulvermaling	Steel Door	Varistar CP
21630-493	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-494	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-495	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-496	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-497	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-498	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-499	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-500	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-501	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-502	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-503	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP
21630-504	RAL 7021	IEC 61587-1	Struktur Pulvermaling	Steel Door	Varistar CP

YDERLIGERE PRODUKTOPLYSNINGER

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE