

# Varistar CP Steel Door, Plain With 3-Point Locking, IP20

## Data Solutions



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection.

### FUNKTIONER

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPECIFIKATIONER

**Locking Type:** 3-Point Locking

**Product Type:** Cabinet Door

**Beskyttelsesgrad:** IP20

**Materiale:** Stål

Table 1/2

| Katalognummer | Rack Height | Højde  | Bredde | Pakke mængde | Farve      | Farvekode |
|---------------|-------------|--------|--------|--------------|------------|-----------|
| 21630-104     | 42U         | 2000mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-105     | 47U         | 2200mm | 600mm  | 1            | Black Grey | RAL 7021  |

| Katalognummer | Rack Height | Højde  | Bredde | Pakke mængde | Farve      | Farvekode |
|---------------|-------------|--------|--------|--------------|------------|-----------|
| 21630-106     | 52U         | 2450mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-107     | 42U         | 2000mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-108     | 47U         | 2200mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-109     | 52U         | 2450mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-432     | 24U         | 1200mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-433     | 24U         | 1200mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-434     | 29U         | 1400mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-435     | 29U         | 1400mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-436     | 33U         | 1600mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-437     | 33U         | 1600mm | 800mm  | 1            | Black Grey | RAL 7021  |
| 21630-438     | 38U         | 1800mm | 600mm  | 1            | Black Grey | RAL 7021  |
| 21630-439     | 38U         | 1800mm | 800mm  | 1            | Black Grey | RAL 7021  |

Table 2/2

| Katalognummer | Complies With            | Finish                | Type       | Works With  |
|---------------|--------------------------|-----------------------|------------|-------------|
| 21630-104     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-105     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-106     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-107     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-108     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |

| Katalognummer | Complies With            | Finish                | Type       | Works With  |
|---------------|--------------------------|-----------------------|------------|-------------|
| 21630-109     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-432     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-433     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-434     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-435     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-436     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-437     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-438     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |
| 21630-439     | IEC 61587-1, IEC 61587-3 | Struktur Pulvermaling | Steel Door | Varistar CP |

## YDERLIGERE PRODUKTOPLYSNINGER

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**