

# Cable to Web of Rail Mold Only, Signal



## FUNKTIONER

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

## SPECIFIKATIONER

**Rail Type:** 85 lb to 141 lb T-Rail Sections

**Materiale:** Graphite

Table 1/1

| Katalognummer | Bond Terminal Style | Conductor Size                | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|---------------|---------------------|-------------------------------|-----------------------------------|--------------|-------------|
| SBB200CLH     | 1" Tab              | 3/16" Bondstrand              | 4.76mm                            | TB5, T21     | Left Hand   |
| SBB200CRH     | 1" Tab              | 3/16" Bondstrand              | 4.76mm                            | TB5, T21     | Right Hand  |
| SBW3150BLH    | 1" Tab              | 3/16" Bondstrand              | 4.76mm                            | TB5          | Left Hand   |
| SBW3150BRH    | 1" Tab              | 3/16" Bondstrand              | 4.76mm                            | TB5          | Right Hand  |
| SBB200YLH     | 1" Tab              | 16 mm <sup>2</sup> Concentric | 5.18mm                            | T21, TB5     | Left Hand   |
| SBB200YRH     | 1" Tab              | 16 mm <sup>2</sup> Concentric | 5.18mm                            | T21, TB5     | Right Hand  |

| Katalognummer | Bond Terminal Style | Conductor Size              | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|---------------|---------------------|-----------------------------|-----------------------------------|--------------|-------------|
| SBB200XRH     | 1" Tab              | 25 mm <sup>2</sup> Stranded | 6.6mm                             | TB5, T21     | Right Hand  |
| SBB200PLH     | 1" Tab              | 35 mm <sup>2</sup> Stranded | 7.75mm                            | TB5, T21     | Left Hand   |
| SBB200PRH     | 1" Tab              | 35 mm <sup>2</sup> Stranded | 7.75mm                            | TB5, T21     | Right Hand  |
| SBWW6LH       | Field-made          | 50 mm <sup>2</sup> Solid    | 8mm                               | T21          | Left Hand   |
| SBWW6RH       | Field-made          | 50 mm <sup>2</sup> Solid    | 8mm                               | T21          | Right Hand  |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**