

Cable to Web of Rail T21 Complete Welder Pair, Signal



FUNKTIONER

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 140 lb. rail

Includes mold cleaner and flint ignitor

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Rail Type	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal
SBTBT21R		Stål, Graphite	UIC	1" Tab	10 mm ² Concentric	4.11mm
SBTBT21B		Stål, Graphite	85 lb to 141 lb T-Rail Sections	3/4" Tab	3/16" Bondstrand	4.76mm
SBTBT21C	165550	Stål, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	3/16" Bondstrand	4.76mm
SBTBT21D		Stål, Graphite	85 lb to 141 lb T-Rail Sections	1 1/2" Tab	3/16" Bondstrand	4.76mm
SBXST21A		Stål, Graphite	85 lb to 141 lb T-Rail Sections	3/4" XS	3/16" Bondstrand	4.76mm

Katalognummer	Artikelnummer	Materiale	Rail Type	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal
SBTBT21Y		Stål, Graphite	UIC	1" Tab	16 mm ² Concentric	5.18mm
SBTBT21L		Stål, Graphite	UIC	1" Tab	22 mm ² Ropelay	6.1mm
SBTBT21X		Stål, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	25 mm ² Ropelay	6.6mm
SBTBT21P		Stål, Graphite	UIC	1" Tab	35 mm ² Concentric	7.75mm
SBTBT21E		Stål, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	5/16" Bondstrand	7.94mm

Table 2/2

Katalognummer	Artikelnummer	Welder Style
SBTBT21R		T21
SBTBT21B		T21
SBTBT21C	165550	T21
SBTBT21D		T21
SBXST21A		T21
SBTBT21Y		T21
SBTBT21L		T21
SBTBT21X		T21
SBTBT21P		T21
SBTBT21E		T21

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE