

Crimping Compression Tool, Battery Powered



FUNKTIONER

Wide cross section range

Ergonomic design

High-performance 18 volt lithium-ion battery for increased work capacity

Automatic retraction stop (ARS) after completed crimping

Lightweight and easy to use

Includes easy-to-carry custom case

SPECIFIKATIONER

Table 1/1

Katalognummer	Artikelnummer	Applied Force	System	Dies	Crimping Shape	Conductor Size
MLB	716920	50kN	Battery-powered hydraulic	RKML series, PKML series	Hexagon	#10 Stranded - 500 kcmil Stranded, 6 mm ² Stranded - 240 mm ² Stranded
M3B	716915	120kN	Battery-powered hydraulic	RKM3 series, PKM3 series	Hexagon	#6 Stranded - 800 kcmil Stranded, 16 mm ² Stranded - 400 mm ² Stranded

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE