

DT2 DIN Rail Surge Protection Class II, 2+0 Mode



CERTIFICERINGER



FUNKTIONER

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance


Red/Green status indication and change-over contacts standard for remote monitoring

SPECIFIKATIONER

Katalognummer	DT230020R
Nominal System Voltage (Un)	240 V
Max Continuous Operating Voltage (Uc)	300 V
Nominal Discharge Current (In), IEC	20kA 8/20 µs
Max Discharge Current (Imax), IEC	50kA 8/20 µs
Voltage Protection Level (Up)	1500V

Katalognummer	DT230020R
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz
Response Time	25 ns Max
Protection Modes	L-PE N-PE
Short Circuit Current Rating (Isccr)	25kA 50kA
Temporary Over Voltage 120 min (Ut/mode)	442 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	337V
Nominal Discharge Current (In), UL	20kA 8/20 µs
Short Circuit Current Rating (SCCR)	150kA
Voltage Protection Rating (VPR)	900V
Technology	Thermal Disconnect
Connection, Solid	35 mm² Max
Connection, Stranded	25 mm² Max
Torque (TQ)	4.5 N·m
Humidity	5 - 95
Temperature	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20
Mounting	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC
Remote Contacts	Yes
Status Indication	Mechanical flag
Dybde (D)	69mm
Height (H)	90 mm
Width (W)	36 mm
Unit Weight	0.27 kg
Certification Details	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 2 IEC® 61643-11 Class II
Replacement Module	DT2300M

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE