

Joint Bond Mold Only, Power



FUNKTIONER

Replacement mold designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

SPECIFIKATIONER

Bond Terminal Style: C

Materiale: Graphite

Table 1/1

Katalognummer	Artikelnummer	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Orientation
MRR50D	547900	UIC54, UIC60	50 mm ² Stranded	9.27mm	Left Hand
MRR50G	547910	UIC54, UIC60	50 mm ² Stranded	9.27mm	Right Hand
PBCS6CWPRHM		85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	Right Hand
PBCS6CWPLHM		85 lb to 141 lb T-Rail Sections	3/0 Composite	14.53mm	Left Hand
PBC2WRHM		85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	Right Hand
PBC2WLHM		85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	Left Hand

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE