


Joint Bond T8 Mold Welder Frame Assembly, Power



FUNKTIONER

Replacement welder frame assembly for T8 joint bond welders

Includes frame with mold lid, mold handle, mold cleaner and flint ignitor

SPECIFIKATIONER

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Table 1/1

Katalognummer	Materiale	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBCT8X6X	Graphite, Steel, Thermoplastic	120 mm ² Ropelay	9.53mm	T8
PBCT82W13X	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T8

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE