

Non-Insulated Stranded Conductor for Lightning Protection



CERTIFICERINGER



FUNKTIONER

Provides a path to ground for lightning currents

SPECIFIKATIONER

Certification Details: UL® 96

Table 1/2

Katalognummer	Materiale	UL Conductor Class	Conductor Type	Number of Wires	Wire Diameter	Diameter
LPA102500	Aluminium	Class I	Smooth Weave	28	1.63mm	13.46 mm
LPA100500	Aluminium	Class I	Smooth Weave	25	1.63mm	12.7 mm
LPC126R250	Copper	Class II	Ropelay	28	1.63mm	11.94 mm

Table 2/2

Katalognummer	Length	Cross Section	Unit Weight	Certificeringer
LPA102500	152.4m	58.31mm ²	0.05 kg	
LPA100500	152.4m	49.98mm ²	0.05 kg	cUL
LPC126R250	76.2m	58.31mm ²	0.17 kg	E202878- Combined_CoC, E202878- Combined_CoC

YDERLIGERE PRODUKTOPLYSNINGER

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

Equivalent Conductor Size	
Part Number	Conductor Size
LPC134xxx	2/0
LPC136xxx	3/0
LPC137xxx	4/0

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE