

nVent ERICO Cadweld Plus Welding Material, F20



nVent ERICO Cadweld Plus Welding Material, F20, allows for an expedited, permanent grounding connection using pre-measured, self-contained cups. Each package of welding material can be easily placed into the mold and safely ignited with the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit to create an irreversible bond.

CERTIFICERINGER



FUNKTIONER

Mixture consists mainly of copper oxide and aluminum

Primarily used in grounding and bonding applications

Integrated welding material package

Color coding by size for easy identification

Electronic ignition

No starting material required

Non-explosive

Not subject to spontaneous ignition

See specific nVent ERICO Cadweld connection details to determine welding material requirements

SPECIFIKATIONER

Table 1/1

Katalognummer	Artikelnummer	Color Code Ring	Complies With	Certificeringer
---------------	---------------	-----------------	---------------	-----------------

15PLUSF20	165700	Black		UL, cUL
400PLUSF20	165711	Brown		
150PLUSF20	165707	Dark Blue	EN IEC® 62561-1 permanent connection	UL, cUL
65PLUSF20	165704	Dark Green	EN IEC® 62561-1 permanent connection	UL, cUL
115PLUSF20	165706	Orange	EN IEC® 62561-1 permanent connection	UL, cUL
25PLUSF20	165701	Red	EN IEC® 62561-1 permanent connection	UL, cUL
32PLUSF20	165702	White	EN IEC® 62561-1 permanent connection	UL, cUL
45PLUSF20	165703	Light Blue	EN IEC® 62561-1 permanent connection	UL, cUL
90PLUSF20	165705	Gray	EN IEC® 62561-1 permanent connection	cUL, UL
500PLUSF20	165712	Light Brown		
300PLUSF20	165710	Light Green		cUL, UL
250PLUSF20	165709	Purple		cUL, UL
600PLUSF20		White		
750PLUSF20	164996	White		
200PLUSF20	165708	Yellow		cUL, UL

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE