

nVent ERICO Ericontact Insertion Tool, Manual



FUNKTIONER

Used to insert single and double nVent ERICO Ericontact Rail Contacts

Packaged in a toolbox for safe and convenient handling

Includes two MDRL (715215) Mandrels for 19 mm nVent ERICO Ericontact

SPECIFIKATIONER

Table 1/1

Katalognummer	Artikelnummer	Applied Force	Operating Pressure	System
HSKE	715345	57kN	630bar	Hydraulic head with manually-operated hydraulic pump

YDERLIGERE PRODUKTOPLYSNINGER

Kit includes: (2) mandrels for 19 mm nVent ERICO Ericontact rail contact, (1) deburr tool, (1) test gauge, (1) metal case, (1) HSKE pump connected with a high pressure hydraulic hose to the PSKE unit, and (1) manual HSKE.

ERICO ERICONTACT Rail Contact Size	Required Parts	
8 mm	MDRL8ADP (715218) Mandrel Adaptor and MDRL8 (715216) Mandrel	Order separately
13.5 mm	MDRL135ADP (715219) Mandrel Adaptor and MDRL135 (715217) Mandrel	Order separately
19 mm	MDRL (715215) Mandrel	Included
22 mm	PSKECMB (715596) Insertion Head Plate	Order separately

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE