

PVT1 Photovoltaic Surge Protection Class I+II



CERTIFICERINGER



FUNKTIONER

Uniquely designed for protection of centralized solar inverters on the DC input side and string boxes

Thermal protection included to ensure safe failure modes


Compact, yet high surge rated pluggable design, using minimum DIN rail width

SPECIFIKATIONER

Katalognummer	PVT11000R	PVT11500R
Max Continuous Operating Voltage (Ucpv)	1100	1500
Nominal Discharge Current (In), IEC	20kA 8/20 μ s	20kA 8/20 μ s
Impulse Current (Iimp)	6.25kA 10/350 μ s	5kA 10/350 μ s
Total Discharge Current (Itotal)	12.5 50	10 40
Voltage Protection Level (Up)	4000V	5000V
Response Time	25 ns Max	25 ns Max
Short Circuit Current Rating (Iscrr)	11kA	11kA

Katalognummer	PVT11000R	PVT11500R
Max Continuous Operating Voltage (Vpdc)	1,100 VDC	1,500 VDC
Voltage Protection Rating (VPR)	2500V	4000V
Nominal Discharge Current (In), UL	20kA 8/20 μ s	20kA 8/20 μ s
Short Circuit Current Rating (SCCR)	50kA	65kA
Protection Modes	-ve to PE -ve to +ve +ve to PE	-ve to PE -ve to +ve +ve to PE
Altitude	2000 m Max	2000 m Max
Humidity	5 - 95	5 - 95
Temperature	-40 to 85 °C	-40 to 85 °C
Connection, Flexible	25 mm ²	25 mm ²
Connection, Solid	35 mm ²	35 mm ²
Connection, Stranded	35 mm ²	35 mm ²
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 125 VAC 1 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC	1 A @ 125 VAC 1 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Dybde (D)	85mm	85mm
Height (H)	90 mm	90 mm
Width (W)	54 mm	54 mm
Unit Weight	0.46 kg	0.5 kg
Replacement Module	PVT1500M PVT1500SM	PVT1750M PVT1750SM
Certification Details	UL® 1449 Edition 4 Type 1CA	UL® 1449 Edition 4 Type 1CA
Complies With	EN IEC 61643-31, Type 1, Type 2	EN IEC 61643-31, Type 1, Type 2

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE