

PVT2 Replacement Module



CERTIFICERINGER



FUNKTIONER

Replacement module for PVT2 photovoltaic surge protection devices

SPECIFIKATIONER

Table 1/2

Katalognummer	Max Continuous Operating Voltage (Ucpv)	Nominal Discharge Current (In), IEC	Total Discharge Current (Itotal)	Voltage Protection Level (Up)	Response Time	Short Circuit Current Rating (Iscrr)
PVT2750M	750V	20kA 8/20 μ s	40	5000V	25 ns Max	11kA
PVT2500M	550V	20kA 8/20 μ s	50	4000V	25 ns Max	11kA

Table 2/2

Katalognummer	Max Continuous Operating Voltage (Vpvc)	Voltage Protection Rating (VPR)	Nominal Discharge Current (In), UL	Short Circuit Current Rating (SCCR)
---------------	---	---------------------------------	------------------------------------	-------------------------------------

PVT2750M	550 VDC	4000V	20kA 8/20 µs	65kA
PVT2500M	550 VDC	3000V	20kA 8/20 µs	50kA

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE