

Rail Drill Machine, Four-Cycle Gas-Powered



The SBM-V range of petrol/gasoline rail drills are designed for smooth, reliable and powerful drilling operation. It works with products of all sizes, from signalling bond hole applications to fishbolt hole sizes. A wide range of accessories are available, including clamping units, drill cutters, and rail profile and special application templates.

FUNKTIONER

Compact and easy to use

Quiet 4-stroke 0.83 horsepower (0.62 kW) engine with a 267 rpm spindle speed

Lightweight design

A range of interchangeable templates to suit all common rail profiles

Uses industry-standard drill cutters

Comes standard with COOLTANKASSY (715375) Rail Drill Machine Coolant Tank and SBMTOOLSET (715395) Rail Drill Machine Tool Set for easy maintenance

Includes metal carrying case

SPECIFIKATIONER

Table 1/1

Katalognummer	Artikelnummer	Fuel	Drill Hole Diameter	Width	Unit Weight
SBMV4	715412	No Mix	7 - 24 mm	381 - 457 mm	13 kg

YDERLIGERE PRODUKTOPLYSNINGER

When ordering a machine, you must also order a rail profile template adapted to the appropriate rail profile and drill-hole position and a clamping device suitable for the rail type and/or clamping method to be selected.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte