

Special Track Work Complete Welder, Power



FUNKTIONER

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFIKATIONER

Rail Type: Crane Rail Profiles

Bond Terminal Style: J

Table 1/1

Katalognummer	Materiale	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation	Handle Length
PBJT503LH	Stål, Graphite	2/0 Concentric	10.62mm	T5	Left Hand	502mm
PBJT52WLH	Stål, Graphite	250 kcmil Ropelay	19.05mm	T5	Left Hand	502mm
PBJT52WRH	Graphite, Stål	250 kcmil Ropelay	19.05mm	T5	Right Hand	502mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE