

Special Track Work Complete Welder, Signal



FUNKTIONER

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

Includes mold cleaner and flint ignitor

SPECIFIKATIONER

Rail Type: Manganese Frog

Table 1/1

Katalognummer	Materiale	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Handle Length
SBTBTB4B	Graphite, Stål	3/4" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4C	Graphite, Stål	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4CL	Graphite, Stål	1" Tab	3/16" Bondstrand	4.76mm	TB4	584.2mm
SBXSTB4A	Graphite, Stål	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4E	Graphite, Stål	1" Tab	5/16" Bondstrand	7.94mm	TB4	381mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE