

Special Track Work Mold Only, Power



FUNKTIONER

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFIKATIONER

Rail Type: Crane Rail Profiles

Materiale: Graphite

Bond Terminal Style: J

Table 1/1

Katalognummer	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT503LHM	2/0 Concentric	10.62mm	T5	Left Hand
PBJT503RHM	2/0 Concentric	10.62mm	T5	Right Hand
PBJT52QLHM	4/0 Concentric	13.41mm	T5	Left Hand
PBJT52QM	4/0 Concentric	13.41mm	T5	Left and Right Hand
PBJT52QRHM	4/0 Concentric	13.41mm	T5	Right Hand

Katalognummer	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT52WLHM	250 kcmil Ropelay	19.05mm	T5	Left Hand
PBJT52WM	250 kcmil Ropelay	19.05mm	T5	Left and Right Hand
PBJT52WRHM	250 kcmil Ropelay	19.05mm	T5	Right Hand

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE