

# Telecom Grounding Busbar



## CERTIFICERINGER



## FUNKTIONER

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

## SPECIFIKATIONER

**Thickness (T):** 6.35 mm

**Width (W):** 50.8 mm

**Materiale:** Copper

Table 1/2


| Katalognummer | Tin Plating | Length 1 (L1) | Length 2 (L2) | Hole Size 1 (HS1) | Hole Size 1 Number of Pairs | Hole Size 2 (HS2) |
|---------------|-------------|---------------|---------------|-------------------|-----------------------------|-------------------|
| TGBA12L06P    | No          | 305 mm        | 229 mm        | 8 mm              | 6                           | 11 mm             |

| Katalognummer | Tin Plating | Length 1 (L1) | Length 2 (L2) | Hole Size 1 (HS1) | Hole Size 1 Number of Pairs | Hole Size 2 (HS2) |
|---------------|-------------|---------------|---------------|-------------------|-----------------------------|-------------------|
| TGBA12L06PT   | Yes         | 305 mm        | 229 mm        | 8 mm              | 6                           | 11 mm             |
| TGBA20L12PT   | Yes         | 508 mm        | 229 mm        | 8 mm              | 12                          | 11 mm             |
| TGBA24L14P    | No          | 610 mm        | 457 mm        | 8 mm              | 14                          | 11 mm             |
| TGBA24L14PT   | Yes         | 610 mm        | 457 mm        | 8 mm              | 14                          | 11 mm             |
| TGBA29L18PT   | Yes         | 737 mm        | 457 mm        | 8 mm              | 18                          | 11 mm             |

Table 2/2

| Katalognummer | Hole Size 2 Number of Pairs | A       | B       | C       |
|---------------|-----------------------------|---------|---------|---------|
| TGBA12L06P    | 3                           | 25.4 mm | 28.6 mm | 15.9 mm |
| TGBA12L06PT   | 3                           | 25.4 mm | 28.6 mm | 15.9 mm |
| TGBA20L12PT   | 3                           | 25.4 mm | 28.6 mm | 15.9 mm |
| TGBA24L14P    | 5                           | 25.4 mm | 28.6 mm | 15.9 mm |
| TGBA24L14PT   | 5                           | 25.4 mm | 28.6 mm | 15.9 mm |
| TGBA29L18PT   | 5                           | 25.4 mm | 28.6 mm | 15.9 mm |

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**