

Universal Transient Barrier, Single Pair



CERTIFICERINGER



FUNKTIONER

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring


Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

SPECIFIKATIONER

Katalognummer	UTB15SP	UTB30SP
Artikelnummer	702862	702863
Nominal System Voltage (Un)	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC
Max Continuous Operating Voltage (Uc)	12 VAC 18 VDC	23 VAC 33 VDC

Katalognummer	UTB15SP	UTB30SP
Rated Load Current (IL)	2A	2A
Frequency	1 MHz	2 MHz
Loop Resistance	1 Ω	1 Ω
Max Discharge Current (Imax), L+L-PE	20kA 8/20 μ s	20kA 8/20 μ s
Protection Modes	Common Differential	Common Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	25 V @ 3 kA	44 V @ 3 kA
Connection, Stranded	1 - 4 mm ²	1 - 4 mm ²
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Temperature	-20 to 65 °C	-20 to 65 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1	IP 20 NEMA®-1
Dybde (D)	72mm	72mm
Height (H)	90 mm	90 mm
Width (W)	12 mm	12 mm
Unit Weight	0.07 kg	0.07 kg
Certification Details	UL® 497B	UL® 497B
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Replacement Module	UTB15SPM	UTB30SPM

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE