

Adjustable Flat Busbar Support Kit



CERTIFICERINGER



FUNKTIONER

Kit includes rail, insulators and mountable extension arms

Adjustable distances between phases

Adjusts quickly to accommodate multiple busbar thicknesses

High resistance to short-circuit forces

Provides excellent electrical protection for equipment

Three phase with neutral circuit

Halogen free

RoHS compliant

SPECIFIKATIONER

Table 1/3

Katalognummer	Artikelnummer	Materiale	Max Working Voltage, IEC (Ui)	Working Temperature	Complies With	Flammability Rating
---------------	---------------	-----------	-------------------------------	---------------------	---------------	---------------------

AFBS-B600	504971	Stål, Aluminum, Glass Fibre Reinforced Polyamide	1000, 1500	-40 to 130 °C	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2- 11 (Glow Wire Test 960 °C)	UL® 94V-0
-----------	--------	---	------------	---------------	--	-----------

Table 2/3

Katalognummer	Artikelnummer	Busbar Width	Busbar Thickness	Height (H)	Width (W)	A
AFBS-B600	504971	30 - 80 mm	5 - 10 mm	70 mm	549 - 749 mm	507 mm

Table 3/3

Katalognummer	Artikelnummer	B	C	Screw Diameter (Sc)	Unit Weight
AFBS-B600	504971	61 - 176 mm	525 - 725 mm	8	2.2 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE