

DH Distance Holder and Spacer



CERTIFICERINGER



FUNKTIONER

To make higher plates, screens or profiles

Male-female allowing stable mounting

Electrotechnical applications

SPECIFIKATIONER

Insulation Voltage:	1000V
Finish:	Electrogalvanized
Flammability Rating:	UL® 94HB
Temperature:	80 °C Max

Table 1/2

Katalognummer	Artikelnummer	Materiale	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Length (L)
DH15M5	560660	Stål, Polystyrene	M5	7mm	7mm	15mm
DH15M6	560740	Stål, Polystyrene	M6	7mm	8mm	15mm

Katalognummer	Artikelnummer	Materiale	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Length (L)
DH20M5	560670	Stål, Polystyrene	M5	7mm	7mm	20mm
DH20M6	560750	Stål, Polystyrene	M6	7mm	8mm	20mm
DH30M5	560600	Stål, Polystyrene	M5	7mm	7mm	30mm
DH30M6	560700	Stål, Polystyrene	M6	7mm	8mm	30mm
DH45M5	560610	Stål, Polystyrene	M5	7mm	7mm	45mm
DH45M6	560710	Stål, Polystyrene	M6	7mm	8mm	45mm
DH55M5	560620	Stål, Polystyrene	M5	7mm	7mm	55mm
DH70M5	560630	Stål, Polystyrene	M5	7mm	7mm	70mm
DH120M5	560650	Stål, Polystyrene	M5	7mm	7mm	120mm
DH70M6	560720	Stål, Polystyrene	M6	7mm	8mm	70mm
DH85M5	560640	Stål, Polystyrene	M5	7mm	7mm	85mm
DH120M6	560730	Stål, Polystyrene	M6	7mm	8mm	120mm

Table 2/2

Katalognummer	Artikelnummer	Width (W)	Unit Weight
DH15M5	560660	13 mm	0 kg
DH15M6	560740	13 mm	0 kg
DH20M5	560670	13 mm	0.01 kg
DH20M6	560750	13 mm	0.01 kg
DH30M5	560600	13 mm	0.01 kg

Katalognummer	Artikelnummer	Width (W)	Unit Weight
DH30M6	560700	13 mm	0.01 kg
DH45M5	560610	13 mm	0.01 kg
DH45M6	560710	13 mm	0.01 kg
DH55M5	560620	13 mm	0.01 kg
DH70M5	560630	13 mm	0.01 kg
DH120M5	560650	13 mm	0.02 kg
DH70M6	560720	13 mm	0.02 kg
DH85M5	560640	13 mm	0.02 kg
DH120M6	560730	13 mm	0.04 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE