

EB-142/166 Earthing and Neutral Busbar



CERTIFICERINGER



FUNKTIONER

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Main terminal clamp available for thicker conductors

Nickel plating is corrosion resistant

Single or dual support brackets available for attaching busbar to DIN rail

Rigid bar

Cut to length as needed

Quick and easy installation

RoHS compliant

SPECIFIKATIONER


Materiale: Brass

Finish: Nickel Plated

Katalognummer	EB166	EB142
---------------	-------	-------

Artikelnummer	568667	568668
Number of Connections	166	142
Conductor Size, IEC	1.5 - 10 mm ² Stranded	1.5 - 16 mm ² Stranded
Max Current Rating	40A	63A
Cross Section	64mm ²	80mm ²
Dybde (D)	8mm	8mm
Height (H)	8 mm	10 mm
Width (W)	1000 mm	1000 mm
Hole Size (HS)	4.5 mm	5.5 mm
Thread Size (TS)	M4	M5
A	6 mm	7 mm
Torque (TQ)	0.89 N·m	2 N·m
Unit Weight	0.47 kg	0.58 kg
Complies With	IEC® 60998-2-1	IEC® 60998-2-1

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE