

FBSS Flat Busbar Support



CERTIFICERINGER



FUNKTIONER

Supports busbars at an angle for easy connections

Includes mounting holes for direct fixing of protection screen

Adjustable arms for easy mounting

Three phase with neutral circuit

Halogen free

SPECIFIKATIONER

Table 1/3

Katalognummer	Artikelnummer	Materiale	Max Working Voltage, IEC (Ui)	Working Temperature	Typical Application Current Rating	Flammability Rating
FBSS32X5	551190	Stål, Glass Fibre Reinforced Polyamide, Aluminum	1000, 1500	-40 to 130 °C	400 A	UL® 94V-0

Table 2/3

Katalognummer	Artikelnummer	Busbar Width	Busbar Thickness	Complies With	Height (H)	Width (W)
FBSS32X5	551190	32 mm	5 mm	IEC® 60695-2-11 (Glow Wire Test 960 °C)	47 mm	338 - 390 mm

Table 3/3

Katalognummer	Artikelnummer	A	B	C	X	Unit Weight
FBSS32X5	551190	325 - 377 mm	290 mm	65 mm	6.5 x 23 mm	0.32 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE