

# FRCB Flat Braid in Coil, Plain Copper



## CERTIFICERINGER



## FUNKTIONER

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

## SPECIFIKATIONER

**Materiale:** Copper

Table 1/2

| Katalognummer | Artikelnummer | Nominal Current | Cross Section      | Number of Wires | Wire Diameter | Length |
|---------------|---------------|-----------------|--------------------|-----------------|---------------|--------|
| FRCB15-10     | 557030        | 75A             | 10mm <sup>2</sup>  | 576             | 0.15mm        | 25m    |
| FRCB15-100    | 557150        | 360A            | 100mm <sup>2</sup> | 5664            | 0.15mm        | 25m    |
| FRCB15-16     | 557040        | 120A            | 16mm <sup>2</sup>  | 896             | 0.15mm        | 25m    |
| FRCB15-25     | 557060        | 150A            | 25mm <sup>2</sup>  | 1404            | 0.15mm        | 25m    |

| Katalognummer | Artikelnummer | Nominal Current | Cross Section     | Number of Wires | Wire Diameter | Length |
|---------------|---------------|-----------------|-------------------|-----------------|---------------|--------|
| FRCB15-35     | 557080        | 200A            | 35mm <sup>2</sup> | 1980            | 0.15mm        | 25m    |
| FRCB15-40     | 557090        | 220A            | 40mm <sup>2</sup> | 2272            | 0.15mm        | 25m    |
| FRCB15-50     | 557100        | 250A            | 50mm <sup>2</sup> | 2848            | 0.15mm        | 25m    |
| FRCB15-75     | 557130        | 300A            | 75mm <sup>2</sup> | 4256            | 0.15mm        | 25m    |

Table 2/2

| Katalognummer | Artikelnummer | Thickness | Width | Unit Weight |
|---------------|---------------|-----------|-------|-------------|
| FRCB15-10     | 557030        | 1.5 mm    | 10 mm | 0.1 kg      |
| FRCB15-100    | 557150        | 4 mm      | 40 mm | 1 kg        |
| FRCB15-16     | 557040        | 1.5 mm    | 15 mm | 0.16 kg     |
| FRCB15-25     | 557060        | 1.5 mm    | 23 mm | 0.25 kg     |
| FRCB15-35     | 557080        | 2.5 mm    | 23 mm | 0.35 kg     |
| FRCB15-40     | 557090        | 2.5 mm    | 25 mm | 0.4 kg      |
| FRCB15-50     | 557100        | 3 mm      | 28 mm | 0.5 kg      |
| FRCB15-75     | 557130        | 4 mm      | 30 mm | 0.75 kg     |

## YDERLIGERE PRODUKTOPLYSNINGER

Unit weight is per meter (3.28').

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**