

HFBT nVent ERIFLEX Flexibar Bending Tool



CERTIFICERINGER



FUNKTIONER

Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation

Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation

Portable tool can be used on the jobsite or attached to a workbench

Includes tool box

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Bending Radius	Bending Angle	Dybde	Height
HFBT	558920	Stål	10mm	180 ° Max	120mm	215 mm

Table 2/2

Katalognummer	Artikelnummer	Width	Unit Weight
HFBT	558920	345 mm	7 kg

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE