

Hydraulic Flexible/Non-Flexible Busbar Work Center, 230 V



CERTIFICERINGER



FUNKTIONER

Mobile workbench for cutting, bending and punching copper busbars or nVent ERIFLEX Flexibar

Includes hydraulic punch, hydraulic busbar cutter, hydraulic bender with programmable angle controller, hydraulic pump with foot controller, calibrated gauge and stop, and two ejection stops

Large stainless steel work surface with collapsible extensions support large copper busbars or nVent ERIFLEX Flexibar

Built-in storage cabinet with lockable door and four drawers for storing accessories

Four-way directional valve makes it possible to quickly switch between tools without disconnecting and reconnecting tools

Includes an additional hydraulic hose and 6 m (19.69') power cord to connect an additional hydraulic tool

Scrap storage bins under work surface

Forklift rail, locking directional wheels and built-in handles provide easy mobility

Protected by an electrical panel control with circuit breaker

SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Height (H)	Length (L)	Width (W)	A	Power Supply Voltage
HYDR-WC-230V	545650	1465 mm	1465mm	770 mm	1380 mm	230

Table 2/2

Katalognummer	Artikelnummer	Unit Weight
HYDR-WC-230V	545650	356 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE