

MDRCPT-2 Manual Din Rail Cutting and Punching Tool



CERTIFICERINGER



FUNKTIONER

Punches slots and cuts DIN rail without burrs or deformation

Punches horizontal and vertical slots

Works with five different types of DIN rail and M6 threaded rod

Includes ruler, guide and end stops

RoHS compliant

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Slot Size	Dybde	Height	Length
MDRCPT-2	559142	Aluminum, Stål	6.5 x 9.5 mm	165mm	200 mm	100mm

Table 2/2

Katalognummer	Artikelnummer	Unit Weight
---------------	---------------	-------------

MDRCPT-2	559142	13 kg
----------	--------	-------

YDERLIGERE PRODUKTOPLYSNINGER

Horizontal slots must be punched a minimum of 8 mm (0.315") from the edge of the DIN rail. Vertical slots must be punched a minimum of 12 mm (0.472") from the edge of the DIN rail.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE