

MFSHT-2 nVent ERIFLEX Flexibar Manual Shearing Tool



CERTIFICERINGER



FUNKTIONER

Cuts nVent ERIFLEX Flexibar quickly and accurately without burrs or deformation

Cuts through the insulation without damaging it

Maximum nVent ERIFLEX Flexibar shearing 5x32x1

Adjustable abutment for identical and repetitive cuttings

Abutment and indicator allow for easy cutting of 45° chamfers

Elastomer edge near the blade helps to prevent jamming from shavings

Replacement blade available

RoHS compliant

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Conductor Thickness	Conductor Width	Dybde	Height
MFSHT-2	559146	Stål, Aluminum	5 mm	32 mm Max	200mm	750 mm

Table 2/2

Katalognummer	Artikelnummer	Width	Unit Weight
MFSHT-2	559146	160 mm	6 kg

YDERLIGERE PRODUKTOPLYSNINGER

Tool must be installed on a table.

Do not use to cut solid busbar.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE