

nVent ERIFLEX Flexidrill Drill Guide



CERTIFICERINGER



FUNKTIONER

Guide for drilling holes into nVent ERIFLEX Flexibar, PBC Braided Power Shunts and PPS Presswelded Power Shunts

Includes dies for mutiple diameters

Adjustable guides allow for multiple hole center to hole center distances

RoHS compliant

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Die Hole Size	Dybde	Height	Width
FLEXIDRILLR	558600	Stål	6.5 mm, 8.5 mm, 10.5 mm, 12.5 mm	300mm	150 mm	250 mm

Table 2/2

Katalognummer	Artikelnummer	Unit Weight
FLEXIDRILLR	558600	9.5 kg

YDERLIGERE PRODUKTOPLYSNINGER

Do not use with nVent ERIFLEX Flexibar Summum.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE