

PDR Perforated Symmetric Profile



CERTIFICERINGER



FUNKTIONER

Rapid assembly of all kinds of frameworks

High mechanical resistance

High corrosion resistance

RoHS compliant

Conforms to EN 60715 and 50022 and DIN 46277

SPECIFIKATIONER

Finish: Electrogalvanized

Materiale: Stål

Table 1/2


Katalognummer	Artikelnummer	Height (H)	Width (W)	Length (L)	Thickness (T)	A
PDR5-2M	557750	15 mm	5.5 mm	2000mm	1 mm	2.25 mm
PDR7-2M	557850	35 mm	7.5 mm	2000mm	1 mm	4 mm

Katalognummer	Artikelnummer	Height (H)	Width (W)	Length (L)	Thickness (T)	A
PDR7-2M-5-2	557855	35 mm	7.5 mm	2000mm	1 mm	4 mm
PDR7-3M	557860	35 mm	7.5 mm	3000mm	1 mm	4 mm
PDR15-2M	557950	35 mm	15 mm	2000mm	1.5 mm	4 mm
PDR15-3M	557960	35 mm	15 mm	3000mm	1.5 mm	4 mm

Table 2/2

Katalognummer	Artikelnummer	B	C	D	Unit Weight
PDR5-2M	557750	7.8 mm	12.2 mm	4.2 mm	0.28 kg
PDR7-2M	557850	7 mm	18 mm	6.2 mm	0.62 kg
PDR7-2M-5-2	557855	11 mm	25 mm	5.2 mm	0.62 kg
PDR7-3M	557860	7 mm	18 mm	6.2 mm	0.92 kg
PDR15-2M	557950	7 mm	18 mm	6.2 mm	1.2 kg
PDR15-3M	557960	7 mm	18 mm	6.2 mm	1.81 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE