

QCC nVent ERIFLEX Flexibar Clamp



CERTIFICERINGER



FUNKTIONER

Connects nVent ERIFLEX Flexibar to punched busbar

Allows for excellent electrical contact

Compact, space saving design

Installs quickly and easily

Ideal for on site modifications

SPECIFIKATIONER

Finish: Electrogalvanized

Materiale: Stål

Table 1/2

Katalognummer	Artikelnummer	Conductor Width	Dybde (D)	Height (H)	Width (W)	Thickness (T)
QCC15-5-32	561210	15.5 - 32 mm	13mm	35 mm	70 mm	5 mm
QCC40-63	561220	40 - 63 mm	13mm	35 mm	95 mm	5 mm

Table 2/2

Katalognummer	Artikelnummer	A	B	C	Unit Weight
QCC15-5-32	561210	50 mm	10.5 mm	11 mm	0.11 kg
QCC40-63	561220	75 mm	10.5 mm	11 mm	0.16 kg

YDERLIGERE PRODUKTOPLYSNINGER

Use one clamp when nVent ERIFLEX Flexibar thickness is less than 5 mm (0.2") and two clamps when nVent ERIFLEX Flexibar thickness is greater than 5 mm (0.2").

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE