

TCB Threaded Busbar With Fixing Slot



CERTIFICERINGER



FUNKTIONER

End slots can be used to fix busbar to a support or connect the main input conductor

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

SPECIFIKATIONER

Materiale: Copper

Table 1/2


Katalognummer	Artikelnummer	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)
TCB15X5-1M	550210	15 mm	5 mm	990mm	M6	6 N·m

Katalognummer	Artikelnummer	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)
TCB20X5-1M	550220	20 mm	5 mm	990mm	M6	6 N·m
TCB20X5-2M	549010	20 mm	5 mm	1985mm	M6	6 N·m
TCB30X5-2M	549020	30 mm	5 mm	1985mm	M6	6 N·m
TCB32X5-1M	550230	32 mm	5 mm	990mm	M6	6 N·m
TCBS15X5-2M	549000	15 mm	5 mm	1985mm	M6	6 N·m

Table 2/2

Katalognummer	Artikelnummer	A	B	C	Unit Weight
TCB15X5-1M	550210	25 mm	12 mm	8 mm	0.65 kg
TCB20X5-1M	550220	25 mm	14 mm	10 mm	0.85 kg
TCB20X5-2M	549010	25 mm	14 mm	10 mm	1.67 kg
TCB30X5-2M	549020	25 mm	16 mm	12 mm	2.5 kg
TCB32X5-1M	550230	25 mm	16 mm	12 mm	1.35 kg
TCBS15X5-2M	549000	17.5 mm	12 mm	8 mm	1.19 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE