

45-graders bøjning i rustfrit stål til gennemføring



Feed-Through Stainless Steel 45-Degree Elbows are for continuous runs with 45-degree turns. Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications.

INDUSTRISTANDARDER

Certified by Canadian Standards Association.

FUNKTIONER

Feed-Through Stainless Steel 45-Degree Elbows are for continuous runs with 45-degree turns

Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications

SPECIFIKATIONER

Finish: No. 2B
Materiale: Stainless Steel 304

Table 1/1

Katalognummer	Type	Højde	Bredde	Tykkelse	Hurtigforsendelse
F66WE45SS	Elbow	152mm	152mm	1.59mm	Nej
F44WE45SS	Elbow	102mm	102mm	1.59mm	Nej

YDERLIGERE PRODUKTOPLYSNINGER

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints. Dimension J is from intersection of center lines.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE