

Dørkontakt til farlige lokationer, LEDHLSW



The Hazardous Location Door Switch is designed to be used with nVent HOFFMAN Hazardous Location LED Lights in Class 1, Division 2 hazardous areas. The included hardware kit allows the door switch to easily be mounted and maintain the enclosure rating up to UL Type 4X. This versatile switch activates the LED light when the enclosure door is opened and can be mounted on any flange of the enclosure. The included five-foot connect cable allows ease of wiring to the enclosure back panel.

INDUSTRISTANDARDE

Switch Rating

Explosion-proof for Class 1, Division 2, Groups A, B, C, and D

FUNKTIONER

Class 1, Division 2 hazardous areas

Maintains the enclosure rating up to UL Type 4X

Five foot connection cable

Ease of wiring to the enclosure back panel

SPECIFIKATIONER

Table 1/1						
Katalognummer	Højde	Bredde	Dybde	Materiale	Finish	Farve
LEDHLSWITCH	10mm	18mm	28mm	Plastik	Smooth	Gray

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE