

Heavy-Duty Swing-Out Rack Frame



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

FUNKTIONER

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

SPECIFIKATIONER

Tykkelse: 2.66mm
Farve: Light Gray
Finish: Struktur Pulvermaling
Farvekode: RAL 7035

Table 1/1

Katalognummer	Materiale	Fits Frame Width	Rack Units	Hurtigforsendelse
PSF76	Lakeret Stål	600mm	10U	Nej
PSF146	Lakeret Stål	600mm	25U	Nej
PSF148	Lakeret Stål	800mm	25U	Nej
PSF78	Lakeret Stål	800mm	10U	Nej
PSF168	Lakeret Stål	800mm	30U	Nej
PSF186	Lakeret Stål	600mm	34U	Nej
PSF188	Lakeret Stål	800mm	34U	Nej
PSF206	Lakeret Stål	600mm	39U	Nej
PSF77	Lakeret Stål	700mm	10U	Nej
PSF207	Lakeret Stål	700mm	39U	Nej
PSF208	Lakeret Stål	800mm	39U	Nej
PSF226	Lakeret Stål	600mm	43U	Nej
PSF227	Lakeret Stål	700mm	43U	Nej
PSF228	Lakeret Stål	800mm	43U	Nej
PSF166	Lakeret Stål	600mm	30U	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE