

Hultætninger af metal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals. Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.

INDUSTRISTANDARDER

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66



FUNKTIONER

Oliebestandig pakning medfølger

Available in multiple colors and sizes

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

SPECIFIKATIONER

Table 1/1						
Katalognummer	Materiale	Finish	Farve	Farvekode	Tykkelse	Hole Diameter
AS056M	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	14mm max
AS056MSS	Stainless Steel 304	Polished			1.5mm	14mm max
ASPBGSS	Stainless Steel 304	Polished			1.5mm	22mm max
AS050	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	22mm max
AS050LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	22mm max
AS075SS	Stainless Steel 304	Polished			1.5mm	27mm max
AS075	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	27mm max
AS075LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	27mm max
ASPBSS	Stainless Steel 304	Polished			1.5mm	32mm max
AS050SS	Stainless Steel 304	Polished			1.5mm	22mm max
AS056CB	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	14mm max
AS100	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	35mm
AS100LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	35mm
AS100SS	Stainless Steel 304	Polished			1.5mm	35mm
ASPB	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	32mm max
ASPB LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	32mm max
AS125	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	43mm max
AS125SS	Stainless Steel 304	Polished			1.5mm	43mm max
AS150SS	Stainless Steel 304	Polished			1.5mm	51mm max

Katalognummer	Materiale	Finish	Farve	Farvekode	Tykkelse	Hole Diameter
AS150	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	51mm max
AS150LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	51mm max
AS200SS	Stainless Steel 304	Polished			1.5mm	64mm max
AS200	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	64mm max
AS200LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	64mm max
AS056MFB	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	14mm max
AS056MLG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	14mm max
AS250SS	Stainless Steel 304	Polished			1.5mm	76mm max
AS250	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	76mm max
AS300SS	Stainless Steel 304	Polished			1.5mm	92mm max
AS300	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	92mm max
ASPBG	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	22mm max
AS350	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	105mm max
AS350SS	Stainless Steel 304	Polished			1.5mm	105mm max
AS400	Lakeret Stål	Struktur Pulvermaling	Gray	ANSI 61	1.5mm	117mm max
AS400SS	Stainless Steel 304	Polished			1.5mm	117mm max
AS125LG	Lakeret Stål	Struktur Pulvermaling	Light Gray	RAL 7035	1.5mm	43mm max

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE