

Almindelige døre | Gulvskabe, DN



Denne dør erstatter bagpanelet i et gulvskab og giver mulighed for adgang bagfra til udstyr, som er monteret i front, eller mulighed for brug af monteringsplader ryg mod ryg for at øge skabets monteringsplads.

FUNKTIONER

Beskrivelse: Standarddør udstyret med dobbelt-bit 3 mm låsesystem og dørramme. DNМК dørtilbehørssæt (hængsler, låsebeslag) skal bestilles separat. Alt ekstraudstyr i låseprogrammet samt 180° hængsler kan benyttes. Kompatibelt med kombinerbare og kompakte skabsserier.

Materiale: 2 mm stålplade.

Maksimal belastning: 800 N.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Monteringskrav: Anvend hængsel sæt DNМК hvis dør ikke tidligere har været monteret.

Pakke størrelse: 1 stk.

SPECIFIKATIONER

Farve: Light Gray
Materiale: Lakeret Stål
Finish: Struktur Pulvermaling
Farvekode: RAL 7035

Table 1/1

Katalognummer	Højde	Bredde	Dybde	Door Type	Enclosure Material	Produktfamilie
DN2210R5	2182mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1106R5	1082mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1206LR5	1182mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1206R5	1182mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1206RR5	1182mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1208R5	1182mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1405LR5	1382mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1405RR5	1382mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1406LR5	1382mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1406R5	1382mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1406RR5	1382mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1408R5	1382mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1606LR5	1582mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1606R5	1582mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1606RR5	1582mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1608R5	1582mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing

Katalognummer	Højde	Bredde	Dybde	Door Type	EnclosureMaterial	Produktfamilie
DN1610R5	1582mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1804LR5	1782mm	393mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1804RR5	1782mm	393mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1805LR5	1782mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1805R5	1782mm	493mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1805RR5	1782mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1806LR5	1782mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1806R5	1782mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1806RR5	1782mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1808LR5	1782mm	793mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1808R5	1782mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1808RR5	1782mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1810R5	1782mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2004LR5	1982mm	393mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2004RR5	1982mm	393mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2005LR5	1982mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2005R5	1982mm	493mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2005RR5	1982mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2006LR5	1982mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2006R5	1982mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing

Katalognummer	Højde	Bredde	Dybde	Door Type	EnclosureMaterial	Produktfamilie
DN2006RR5	1982mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2008LR5	1982mm	793mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2008R5	1982mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2008RR5	1982mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2010R5	1982mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2205LR5	2182mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2205RR5	2182mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2206LR5	2182mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2206R5	2182mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2206RR5	2182mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2208R5	2182mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1804R5	1782mm	393mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2004R5	1982mm	393mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2204R5	2182mm	393mm	17mm	Plain	Lakeret Stål	Free-Standing

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE