

ProLine Gland Plate



Adjustable Gland Plates are used to seal the bottom of the ProLine frame. Solid, vented and shielded Gland Plates are available. Solid and filtered gland plates include covers that are gasketed to maintain Type 12 enclosure requirements. All installation hardware is included. Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed. EMC Gland Plate maintains a Type 1 rating.

FUNKTIONER

Solid Gland Plate and EMC Gland Plate are accessories to 100- mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed.

Solid Gland Plate: the Solid Gland Plate can be used with all ProLine subpanels or rack angles. The gland plate consists of a base mounting surface and two adjustable foam-gasketed plates that permit cable entry. The plate can be rotated 180 degrees for front or rear cable entry.

EMC Gland Plate: This gland plate can be used with subpanels or rack angles. Gland plate consists of a base mounting surface and two adjustable gland plates (both have a conductive coating) with conductive fabric-over-foam gasket for cable entry.

Filtered (Vented) Gland Plate: Filtered Gland Plate is used only in conjunction with Vented Plinth Base Covers. The plate can be used with all ProLine subpanels or rack angles. It consists of a mounting base, three adjustable plates for cable entry, a filter and filter retaining rails. Manufactured from 16 gauge steel and finished with RAL 7035 textured light-gray polyester powder paint. Replacement filters available. EMC Gland Plate maintains a Type 1 rating.

All hardware included

SPECIFIKATIONER

Tykkelse: 1.9mm
Farve: Light Gray
Farvekode: RAL 7035

Table 1/1

Katalognummer	Materiale	Fits Frame Width	Fits Frame Depth	Finish	Hurtigforsendelse
PGP66	Lakeret Stål	600mm	600mm	Struktur Pulvermaling	Nej
PGPV66	Lakeret Stål	600mm	600mm	Struktur Pulvermaling	Nej
PGPV68	Lakeret Stål	600mm	800mm	Struktur Pulvermaling	Nej
PGP68	Lakeret Stål	600mm	800mm	Struktur Pulvermaling	Nej
PGPV85	Lakeret Stål	800mm	500mm	Struktur Pulvermaling	Nej
PGP85	Lakeret Stål	800mm	500mm	Struktur Pulvermaling	Nej
PGPV88	Lakeret Stål	800mm	800mm	Struktur Pulvermaling	Nej
PGP88	Lakeret Stål	800mm	800mm	Struktur Pulvermaling	Nej
PGPV64	Lakeret Stål	600mm	400mm	Struktur Pulvermaling	Nej
PGP64	Lakeret Stål	600mm	400mm	Struktur Pulvermaling	Nej
PGPV86	Lakeret Stål	800mm	600mm	Struktur Pulvermaling	Nej
PGP86	Lakeret Stål	800mm	600mm	Struktur Pulvermaling	Nej
PGP105	Lakeret Stål	1000mm	500mm	Struktur Pulvermaling	Nej
PGPV106	Lakeret Stål	1000mm	600mm	Struktur Pulvermaling	Nej
PGP106	Lakeret Stål	1000mm	600mm	Struktur Pulvermaling	Nej
PGPV108	Lakeret Stål	1000mm	800mm	Struktur Pulvermaling	Nej
PGP108	Lakeret Stål	1000mm	800mm	Struktur Pulvermaling	Nej

Katalognummer	Materiale	Fits Frame Width	Fits Frame Depth	Finish	Hurtigforsendelse
PGP84	Lakeret Stål	800mm	400mm	Struktur Pulvermaling	Nej
PGPV65	Lakeret Stål	600mm	500mm	Struktur Pulvermaling	Nej
PGP65	Lakeret Stål	600mm	500mm	Struktur Pulvermaling	Nej
PGPV76	Lakeret Stål	700mm	600mm	Struktur Pulvermaling	Nej
PGP78	Lakeret Stål	700mm	800mm	Struktur Pulvermaling	Nej
PGPV78	Lakeret Stål	700mm	800mm	Struktur Pulvermaling	Nej
PGPV89	Lakeret Stål	800mm	900mm	Struktur Pulvermaling	Nej
PGP89	Lakeret Stål	800mm	900mm	Struktur Pulvermaling	Nej
PGP79	Lakeret Stål	700mm	900mm	Struktur Pulvermaling	Nej
PGP104	Lakeret Stål	1000mm	400mm	Struktur Pulvermaling	Nej
PGP105AHF	Lakeret Stål	1000mm	500mm	Galvaniseret	Nej
PGP108AHF	Lakeret Stål	1000mm	800mm	Galvaniseret	Nej
PGP124	Lakeret Stål	1200mm	400mm	Struktur Pulvermaling	Nej
PGP125	Lakeret Stål	1200mm	500mm	Struktur Pulvermaling	Nej
PGP126	Lakeret Stål	1200mm	600mm	Struktur Pulvermaling	Nej
PGP128	Lakeret Stål	1200mm	800mm	Struktur Pulvermaling	Nej
PGP164	Lakeret Stål	1600mm	400mm	Struktur Pulvermaling	Nej
PGP165	Lakeret Stål	1600mm	500mm	Struktur Pulvermaling	Nej
PGP166	Lakeret Stål	1600mm	600mm	Struktur Pulvermaling	Nej
PGP168	Lakeret Stål	1600mm	800mm	Struktur Pulvermaling	Nej

Katalognummer	Materiale	Fits Frame Width	Fits Frame Depth	Finish	Hurtigforsendelse
PGP185	Lakeret Stål	1800mm	500mm	Struktur Pulvermaling	Nej
PGP186	Lakeret Stål	1800mm	600mm	Struktur Pulvermaling	Nej
PGP188	Lakeret Stål	1800mm	800mm	Struktur Pulvermaling	Nej
PGP45	Lakeret Stål	400mm	500mm	Struktur Pulvermaling	Nej
PGP46	Lakeret Stål	400mm	600mm	Struktur Pulvermaling	Nej
PGP64AHF	Lakeret Stål	600mm	400mm	Galvaniseret	Nej
PGP65AHF	Lakeret Stål	600mm	500mm	Galvaniseret	Nej
PGP66AHF	Lakeret Stål	600mm	600mm	Galvaniseret	Nej
PGP68AHF	Lakeret Stål	600mm	800mm	Galvaniseret	Nej
PGP78AHF	Lakeret Stål	700mm	800mm	Galvaniseret	Nej
PGP79AHF	Lakeret Stål	700mm	900mm	Galvaniseret	Nej
PGP88AHF	Lakeret Stål	800mm	800mm	Galvaniseret	Nej
PGP89AHF	Lakeret Stål	800mm	900mm	Galvaniseret	Nej
PGPV125	Lakeret Stål	1200mm	500mm	Struktur Pulvermaling	Nej
PGPV126	Lakeret Stål	1200mm	600mm	Struktur Pulvermaling	Nej
PGPV128	Lakeret Stål	1200mm	800mm	Struktur Pulvermaling	Nej
PGPV165	Lakeret Stål	1600mm	500mm	Struktur Pulvermaling	Nej
PGPV166	Lakeret Stål	1600mm	600mm	Struktur Pulvermaling	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE