

Shelf for air circuit-breakers (ACB) | Strømfordeling, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit breakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

FUNKTIONER

Beskrivelse: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Materiale: 2 mm galvanised steel.

Levering inkluderer: 1 piece with mounting material.

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

d with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections it can not be use

Includes mounting hardware

SPECIFIKATIONER

Tykkelse: 2mm
Materiale: Lakeret Stål
Finish: Plated

Table 1/1

| Katalognummer | Højde | Bredde | Dybde | Monteringspladen s bredde | Maksimal monteringsdybde | Enclosure Material |
|---------------|-------|--------|-------|------------------------------|-----------------------------|-----------------------|
| MSCC0606 | 78mm | 600mm | 600mm | 504mm | 283mm | Lakeret Stål |
| MSCC0806 | 78mm | 800mm | 600mm | 704mm | 283mm | Lakeret Stål |
| MSCC1006 | 78mm | 1000mm | 600mm | 904mm | 283mm | Lakeret Stål |

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE