

Kobling til vinkel, HMI, let, S1MFEC



Suspend 180-Max Flange Elbow Coupling attaches directly to the enclosure for applications where a vertical tube is not required. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The flange elbow coupling has a safety stop and maintenance-free bearings.

FUNKTIONER

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFIKATIONER

Materiale: Aluminium
Finish: Struktur Pulvermaling

Table 1/1						
Katalognummer	Højde	Bredde	Dybde	Farve	Farvekode	Hurtigforsendelse
S1MFECG	138mm	125mm	124mm	Light Gray	RAL 7035	Nej
S1MFEC	138mm	195mm	125mm	Jet Black	RAL 9005	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE