

Universal Busbar Supports, EUBS



This busbar support, EUBS, is available for one, two, or three bars up to 120 x 10 mm. The support can be mounted either at the top or bottom of the enclosure. It is available off the shelf and tested according to IEC 61439. This support is required when a high level of mounting flexibility is required.

FUNKTIONER

Description: Busbar support up to 4500A to be mounted horizontally or vertically. Mounts directly to the enclosure frame or with help of CLPF profiles. Available in one/two/three bars per phase for bar thickness 10 mm, and width from 30 to 120 mm.

Working temperature: -40°C up to 130°C.

Material: Reinforced polyamide and steel. Halogen free.

Delivery: Busbar support with mounting material.

SPECIFIKATIONER

Table 1/1						
Katalognummer	Busbar Thickness	Busbars per Phase	Busbar Width	Materiale	Finish	Farve
EUBS310TN	10mm min	3Ph min	30 – 125mm	Stål, Polyamide	Plated	Black
EUBS110TN	10mm min	1Ph min	30 – 125mm	Stål, Polyamide	Plated	Black
EUBS210TN	10mm min	2Ph min	30 – 125mm	Stål, Polyamide	Plated	Black

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE