

D14 Mechanical Anchor for Cryogenic Applications



The nVent LENTON brand of cryogenic reinforcement splicing systems should be specified whenever cryogenic-grade reinforcing bar is used, or during normal operating or emergency conditions where the temperature falls below - 20 °C (-4 °F). By combining the nVent LENTON taper-threaded couplers with state-of-the-art materials, we have developed one of the slimmest couplers on the market, while still maintaining top performance. Typical construction projects include LNG and LPG storage tanks.

FUNKTIONER

Replaces conventional hooked reinforcing bar

Simplifies reinforcing bar placement and lowers placing costs

Head area exceeds 10x bar area (net 9x)

Improved performance and reliability at cryogenic temperatures (-168 °C / -270 °F)

SPECIFIKATIONER

Finish: Plain

Materiale: Stainless Steel 431 (EN 1.4057)

Table 1/2

Katalognummer	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Length 1 (L1)
EL12D14CRN	12 mm	#4	10M	45 mm		19 mm
EL16D14CRN	16 mm	#5	15M	55 mm		24 mm
EL28D14CRN	28 mm	#9	30M	95 mm	80 mm	42 mm
EL20D14CRN	20 mm	#6	20M	65 mm		35 mm

Katalognummer	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter 1(Ø1)	Diameter 2(Ø2)	Length 1 (L1)
EL32D14CRN	32 mm	#10		105 mm	80 mm	46 mm
EL25D14CRN	25 mm	#8	25M	80 mm		40 mm

Table 2/2

Katalognummer	Length 2 (L2)	Unit Weight
EL12D14CRN		0.21 kg
EL16D14CRN		0.46 kg
EL28D14CRN	20 mm	2.08 kg
EL20D14CRN		0.81 kg
EL32D14CRN	25 mm	2.33 kg
EL25D14CRN		1.57 kg

Designed to Meet: ACI 318;AS3600;ASTM A970;EN 14620-3

YDERLIGERE PRODUKTOPLYSNINGER

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Thread does not need to be flush with end of nVent LENTON Terminator. Thread may be +/- 2 threads from backside of coupler.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE