

# P14 Position Coupler, Male and Nut Only, Worldwide Design



Used in segmental pour and closure pour applications. Male and female components are sold separately.

## FUNKTIONER

Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is free to move in its axial direction

## SPECIFIKATIONER

**Finish:** Plain  
**Coupler Adjustment:** Standard  
**Materiale:** Stål

Table 1/2

| Katalognummer | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | A     |
|---------------|--------------------|----------------|--------------------|--------------|------------|-------|
| EL10P14LMN    | 10 mm              | #3             |                    | 20 mm        | 69mm       | 49 mm |
| EL12P14LMN    | 12 mm              | #4             | 10M                | 20 mm        | 72mm       | 48 mm |
| EL14P14LMN    | 14 mm              |                |                    | 20 mm        | 76mm       | 50 mm |
| EL16P14LMN    | 16 mm              | #5             | 15M                | 25 mm        | 81mm       | 54 mm |
| EL18P14LMN    | 18 mm              |                |                    | 25 mm        | 88mm       | 60 mm |

| Katalognummer | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | A      |
|---------------|--------------------|----------------|--------------------|--------------|------------|--------|
| EL20P14LMN    | 20 mm              | #6             | 20M                | 30 mm        | 108mm      | 72 mm  |
| EL22P14LMN    | 22 mm              | #7             |                    | 35 mm        | 114mm      | 76 mm  |
| EL25P14LMN    | 25 mm              | #8             | 25M                | 35 mm        | 120mm      | 78 mm  |
| EL28P14LMN    | 28 mm              | #9             | 30M                | 40 mm        | 124mm      | 81 mm  |
| EL32P14LMN    | 32 mm              | #10            |                    | 45 mm        | 138mm      | 91 mm  |
| EL36P14LMN    | 36 mm              | #11            | 35M                | 50 mm        | 146mm      | 97 mm  |
| EL40P14LMN    | 40 mm              |                |                    | 55 mm        | 155mm      | 104 mm |


| Table 2/2     |                |                  |             |
|---------------|----------------|------------------|-------------|
| Katalognummer | Bar Depth (BD) | Thread Size (TS) | Unit Weight |
| EL10P14LMN    | 18mm           | M18              | 0.16 kg     |
| EL12P14LMN    | 19mm           | M18              | 0.16 kg     |
| EL14P14LMN    | 21mm           | M18              | 0.16 kg     |
| EL16P14LMN    | 24mm           | M22              | 0.26 kg     |
| EL18P14LMN    | 29mm           | M24              | 0.31 kg     |
| EL20P14LMN    | 35mm           | M26              | 0.46 kg     |
| EL22P14LMN    | 37mm           | M31              | 0.69 kg     |
| EL25P14LMN    | 40mm           | M34              | 0.77 kg     |
| EL28P14LMN    | 42mm           | M37              | 0.99 kg     |
| EL32P14LMN    | 45mm           | M42              | 1.48 kg     |

| Katalognummer | Bar Depth (BD) | Thread Size (TS) | Unit Weight |
|---------------|----------------|------------------|-------------|
| EL36P14LMN    | 52mm           | M46              | 1.86 kg     |
| EL40P14LMN    | 57mm           | M53              | 2.41 kg     |

## YDERLIGERE PRODUKTOPLYSNINGER

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**