

19" Fan Unit, 1 U, With Front Switch

Power Utilities

Front-mounted, illuminated mains switch on AC devices, coupled with additional rear mains outlet; mechanical strain relief for mains input and mains output cables.



CERTIFICATIONS



FEATURES

Can be adapted to subracks

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC
10713-108	230 V min	
10713-110	115 V min	
10713-112	230 V min	
10713-114	115 V min	

Catalog Number	Input Voltage AC	Input Voltage DC
10713-111		24 V min
10713-115		24 V min

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE