

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

KATALOGNUMMER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

FUNKTIONER

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUKTEGENSKABER

Product Type: Cabinet Door

Produktfamilie: Varistar CP

Type: Steel Door, Perforated

Works With: Varistar CP

Locking Type: Single Point Locking

Farve: Black Grey

Farvekode: RAL 7021

Rack Height: 29 U

Højde: 1400 mm

Bredde: 800 mm

Beskyttelsesgrad: IP20

Complies With: IEC 61587-1

YDERLIGERE PRODUKTOPLYSNINGER

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE